

EINSTEIN SAPANA

ASHTEDental 



wireless intraoral camera

- Wireless
- 1.3 Megapixel High Resolution
- Auto Focus
- Onboard Memory
- Super Magnification
- Connect to TV, PC, Video, USB
- Anti Fog Lens
- TWAIN Compliant
- Optional Macro lens for 50x zoom

SUPPLY

INTEGRATE

SUPPORT

We don't just  
SUPPLY you  
with the products  
We FUSE YOUR  
PRACTICE into  
a powerful network system!

Tel: 866.274.8351 > [ashtedental.com](http://ashtedental.com)

7950 Cherry Ave,  
Suite 103,  
Fontana, CA 92336



# SAPANA WIRELESS CAMERA

## High Resolution

**1.36-Megapixel CCD.** Super high quality CCD developed for intraoral images, produce more realistic color, higher resolution, and more natural gradation sequence.

**Processor.** New SX630 data processor was specially developed for intraoral images. It processes the image data from CCD sensor to deliver more smooth, low noise images with realistic color.

## Simple Operation

**Finger Tip Operation- Instant Capture >>> Slideshow**  
High quality images can be instantly captured and stored in the camera by single click on the freeze button. Slide the button to review with your patients.

**On Board Memory.** It holds 16 images in its on board memory for instant review.

**White LED Light.** The LED lights maintain the brightness and original realistic colors for more clear and accurate intraoral images. The LED lights do not require bulb replacement and it reduces the maintenance cost in your office.

## Image Clarity

**Auto Focus.** No manual focusing is required. The camera instantly adjusts focus from an arch to one tooth.

**Anti-Fogging Lens.** The 0.02-inch pin lens solves the problem of condensation, which occurs when patient's breath makes contact with the lens.

## Specifications

Length:	10.2"
Weight:	4.4oz.
Battery Life	1 hr. battery run time
Memory	16-image memory capacity

## Includes:

- Recharging Stand x1
- Disposable Camera Covers x100
- Wireless Receiver



## With TV

Super high quality CCD produces realistic color, higher resolution, and natural gradation sequence.



## With Computer

Plug into your computer's video capture board and download the images straight into the dental imaging software.



## Super Magnification Macro Lens

The optional 50x magnification cap vividly displays small cracks and fractures on teeth.



MACRO LENS CAP  
Autoclavable



50x Magnification

Tel: 866.274.8351 > [ashteldental.com](http://ashteldental.com)

Digital Radiography




Digital Panoramic



Imaging Software



Cone Beam CT



Wireless Camera



Networking

