Technology Integration = Function



Marine grade

plywood base with

stainless steel facing

Door noise reduction

Optima[®] sensor

activated electronic





Belmont

7950 Cherry Ave. Suite 103, Fontana, CA 92336 **866.274.8351 • f 951.848.9700** www.ashteldental.com

ETL Listed


Models and specifications are subject to change without notice.

Optional equipment and features shown.

Copyright© 8/04 Belmont Equipment. BRH00020 REV082004

















Maximized upper storage with 14 tempered glass shelves. Front fascia design enables total utilization of technology.


> Task light diffuser panel eliminates shadows.



The D-66CM shown with BDS-2561 unit mounted to multi-directional sliding work surface.







Integrated clock/timer



D-4RH

Optional bi-fold

doors conceal X-ray

compartment that

is accessible from

both sides. Shown

with 507N Clesta™

BelRay™ X-ray.

light and model 096

Vertical Storage Concepts are a Key to Ergonomic Interaction

Countertop Optional Cambria consists of 93% pure natural Quartz, with a diamondlike hardness. Cambria * provides a non-porous work

surface.

Cambria °



■ Wall Mount Storage

D-2U Upper section D-2L Lower section D-2 Upper/lower section

Flexible

Design = Productivity

D-4RH

Dual center island gives you many options.